



Compact Jerrycans



Compact jerrycan | for more content on less shelf width





The compact jerrycan is ideal as a space-saving canister with its width of 6.5 cm or 12.5 cm. Different liquids can be stored and decanted in a small space. The compact jerrycan can also be stored lying on its side e. g. in a refrigerator. It is very stable due to ribbed structure and thick sides. Using the support stand (only for 5 I canister) for two or three canisters, any number of canisters can safely be placed in the open. The compact jerrycan can also be used as a settling canister.

- With or without threaded connector 3/4"
- PP, transparent
- With tamper-proof closure
- Canister without stopcock autoclavable
- With moulded, indestructible liter graduation
- Canister support made of aluminium for secure stand as accessory (only for 5 l canister)
- Spigot StopCock with rotatable discharge angle and Compact spigot, which fits canisters equipped with glands with threads 3/4", available as accessory

Model	Capacity I	Width mm	Depth mm	Height mm	Opening dia. mm	ltem no.	
without threaded connector	5	65	335	335	41	0435-1050	N4
with threaded connector 3/4"	5	65	335	335	41	0435-2050	N4
without threaded connector	10	125	335	335	41	0435-1100	N4
with threaded connector 3/4"	10	125	335	335	41	0435-2100	N4
Accessories							
Description						Item no.	
Support stand for two compact jerrycans (only for 5 l canister)					0435-9102	N4	
Support stand for three compact jerrycans (only for 5 l canister)					0435-9103	N4	
Venting valve in screw cap					0435-9200	N4	
StopCock angled						0525-1000	N4
Compact spigot						0530-1000	N4
Closure cap 3/4"						0600-0090	N4



Compact Jerrycans



Compact jerrycan, electroconductive






The compact jerrycan, made of electrically conductive HDPE, is especially well suited for use in explosion-proof areas. With a specific surface resistance of $<10^5$ ohms, the canister has a very high electrical conductivity. When correctly earthed, it prevents the danger of ignition due to an accumulation of electrostatic charge. The canister thus helps to meet the requirements of the ATEX 137, TRBS2153 and CENELEC 50404 guidelines.

The plastic industrial canister is non-rusting and can be disposed of with no problems in the recycling system. It can be used for dispensing and storing combustible and highly flammable liquids of explosion groups IIA, IIB and IIC such as laboratory waste in industrial applications or mining.

Due to its narrow width of 6.5 cm or 12.5 cm, the space-saving canister requires very little room, making it suitable for use in very confined spaces. The ribbed structure and thick sides make it very stable and also allow for flat storage. The ergonomic handle ensures secure handling and easy transport. For the version with 3/4" threaded connector, a stop cock can be mounted, for example the StopCock PA, which is electrically conductive.



- With or without threaded connector 3/4"
- Canister support made of aluminium for secure stand as accessory (only for 5 I canister)





Caution! When working with combustible liquids, the canister must be earthed! Use anti-static set!

Model	Capacity I	Width mm	Depth mm	Height mm	ltem no.	
without threaded connector	5	65	335	335	0435-1055	N4
without threaded connector	10	125	335	335	0435-1105	N4
with threaded connector 3/4"	5	65	335	335	0435-2055	N4
with threaded connector 3/4"	10	125	335	335	0435-2105	N4
Accessories						
Description					Item no.	
Anti-static set					5602-1000	N4
Support stand for two compact jerrycans (only for 5 l canister)					0435-9102	N4
Support stand for three compact jerrycans (only for 5 l canister)					0435-9103	N4
StopCock PA, electroconductive					0525-1100	N4

Compact Jerrycans

Bürkle GmbH Rheinauen 5 | D - 79415 Bad Bellingen Phone +49 (0) 76 35 8 27 95-0 Fax +49 (0) 76 35 8 27 95-31 info@buerkle.de | www.buerkle.de



Compact jerrycan & StopCock set

The Compact jerrycan & StopCock set consists of the compact jerrycan with glands 5 I (0435-2050) or 10 I (0435-2100) and the spigot StopCock (0525-1000).



Capacity I	Item no.	
5	0435-0001	N4
10	0435-0010	N4

You Tub

Compact jerrycan & Compact stop cock set

The Compact stop cock is the ideal addition to the compact jerrycan – for perfect storage and filling when space is at a premium! The space-saving set consists of the compact jerrycan with glands 5 l (0435-2050) or 10 l (0435-2100) and the spigot Compact (0530-1000).





DEK

Capacity I	Item no.	
5	0435-3000	N4
10	0435-3010	N4

Compact jerrycan set, electroconductive

The electrically conductive compact jerrycan set consists of a compact jerrycan with a capacity of 5 litres (0435-2055) or 10 litres (0435-2105) and a StopCock PA (0525-1100). The stopcock and canister can be earthed with an anti-static set and can therefore be used in explosion-proof areas. Caution! When working with combustible liquids, the canister must be earthed! Use anti-static set!



Capacity I	Item no.	
5	0435-0005	N4
10	0435-0015	N4
Accessories		
Description	Item no.	
Anti-static set	5602-1000	N4